



• • •••

The 7305 model is available in two options; the 7305P-U with a 800ml disposable collection bottle or the 7305P-US with a 1200ml re-usable collection bottle. The VacuAide can be used from its internal battery or directly from the power supply.

- Uses a rechargeable battery with 60 minutes run time
- Automatically recharges when connected to the power supply
- 12 V DC capability for vehicle charging

- Bronchial / Oral Hygiene
- Provides effective airways clearance
- Helps to control infection



S P E C I F I C A T I O N S

-€, f, „
22.9 x 17.8 x 20.3 cm

f
2.9 kg

...
80 - 550 mm Hg

27 l/min.

60 min.

• ...
0° C - 40° C

† ... ‡
100 - 240 V AC, 50 / 60 Hz

- •
- High performance capabilities with a vacuum range of 80 - 550 mmHg and a flow range of 0 - 27 l/min.
- Meets the stringent ISO 10079-1 standard.
- Comes complete with a rechargeable battery, 12 V DC in car charger, UK mains lead and carry case.
- Has a switch mode power supply allowing operation on any AC voltage 100 V - 240 V.
- Has an integrated bacterial filter.
- Automatic float shut-off to prevent overflow into the unit
- Available with an 800ml disposable or a 1200ml reusable collection bottle



1200 ml re-usable collection bottle



7305P-U with 800ml disposable bottle



Distributor: